

Specification Sheet

Part Number: 556-83018

TAGLF is a limited fire hazard Tiptag that can be used in confined spaces where fire is a concern.

Halogen free so that it will not release toxic fumes if exposed to fire.

TAGLF is a low-smoke, low fire hazard product for use in any confined space where cable identification is critical.

Product Image

Tiptag, Halogen Free, 20mm x 51mm, 4 holes, White, 1000 per roll

Article Number	556-83018
----------------	-----------

Type	TAGLF20X51-4
------	--------------

Color	White (WH)
-------	------------

Quantity Per	pack
--------------	------

Product Description	TAGLF is a Tiptag that is designed for confined spaces, such as rail cars, where a low smoke, low fire hazard marker is required. The TAGLF is Halogen free and will not release harmful fumes when burned.
---------------------	---

Short Description	Tiptag, Halogen Free, 20mm x 51mm, 4 holes, White, 1000 per roll
-------------------	--

Global Part Name	TAGLF20X51-4-PO-X-WH
------------------	----------------------

Length L (Imperial)	2.0
---------------------	-----

Length L (Metric)	51.5
Fixation Method	Others
Variant	Roller form
Width W (Imperial)	0.79
Width W (Metric)	20.4
Height H (Imperial)	0.78
Width of Liner (Metric)	90.0
Width of Liner (Imperial)	3.50
Cable Tie Width Max (Metric)	4.6
Material	Polyolefin, cross-linked (PO-X)
Material Shortcut	PO-X
Flammability	ASTM D635
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only

Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	EN [45545-2] SAE - AS81531 MIL-STD-202G Method 215K ASTM E 162 ASTM E 662 ASTM 1354
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3920990000
Labels per Column	1

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com