

Specification Sheet

Part Number: 556-03069



OEM products ensure 100 percent compatibility and the longest service life.

Industrial-strength cutter option cuts ShrinkTrak, label stock and continuous vinyl for any application.

Replacement ribbon holder comes in a package of two.

Order print heads to match printer model; TTM430 delivers 300 DPI resolution and TTM460 produces 600 DPI.

Kits include hard-shell case to protect printer from debris and impact during transport.

TTM460-S Replacement Print Head, 600 DPI, Silver, 1/pkg

Article Number	556-03069
Type	TTM430SPH600
Color	Various (MIX)
Quantity Per	pack
Product Description	OEM accessories are specifically designed for use with the TT430 and TT460 Series thermal transfer printers. For guaranteed performance and warranty protection, use only the HellermannTyton parts and accessories designed for your specific printer model.

Short Description	TTM460-S Replacement Print Head, 600 DPI, Silver, 1/pkg
-------------------	---

Global Part Name	TTM430SPH600-DIV-MIX
------------------	----------------------

Length L (Imperial)	5.25
---------------------	------

Length L (Metric)	133.35
-------------------	--------

Variant	Print head
---------	------------

Width W (Imperial)	1.75
--------------------	------

Width W (Metric)	44.45
------------------	-------

Height H (Imperial)	1.25
---------------------	------

Height H (Metric)	31.75
-------------------	-------

Material	Various (DIV)
----------	---------------

Material Shortcut	DIV
-------------------	-----

UV Resistant (Yes/No)	No
-----------------------	----

Use Conditions	For Indoor Use Only
----------------	---------------------

Operating Temperature	+40°F to +104°F (+4°C to +40°C)
-----------------------	---------------------------------

Reach Compliant (Article 33)	Yes
------------------------------	-----

ROHS Compliant	Yes
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	8443992250

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)