

Specification Sheet

Part Number: 558-10002

HellermannTyton inkjet ink dries immediately on these labels to reduce or eliminate smearing.

Polyester material resists a wide range of chemicals and solvents. BS5609 synthetic paper available to meet strict marine and maritime labeling requirements.



Can be printed multiple colors, reducing the typical inventory of labels with colored headers and the frequent need to switch stock.

Inkjet Die Cut Roll, 4" x 2", White, Polyester, 150/roll

Article Number	558-10002
----------------	-----------

Type	HT4x2IJWP
------	-----------

Color	White (WH)
-------	------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton inkjet label rolls provide flexible options for creating full-color, chemical-resistant labels of all types. Die-cut labels come with rounded corners, ready to print safety, warning and arc-flash labeling. TagPrint® Pro software allows full-color printing of text and images. Using HellermannTyton inkjet labels saves the time and cost of ordering custom signs online, providing on-demand convenience with no minimums or long lead times.
---------------------	--

Short Description	Inkjet Die Cut Roll, 4" x 2", White, Polyester, 150/roll
-------------------	--

Global Part Name	HT4x2IJWP-PET-WH
------------------	------------------

Width W (Imperial)	4.0
--------------------	-----

Width W (Metric)	101.6
------------------	-------

Thickness T (Imperial)	.007
------------------------	------

Thickness T (Metric)	64.0
----------------------	------

Height H (Imperial)	2.0
---------------------	-----

Height H (Metric)	50.8
-------------------	------

Width of Liner (Metric)	101.6
-------------------------	-------

Width of Liner (Imperial)	4.0
---------------------------	-----

Material	Polyester (PET)
----------	-----------------

Material Shortcut	PET
-------------------	-----

Adhesive	Acrylic
----------	---------

Halogen Free	Yes
--------------	-----

UV Resistant (Yes/No)	No
-----------------------	----

Use Conditions	For Indoor Use Only
Adhesive Operating Temperature	-40°F to +300°F (-40°C to +149°C)
Operating Temperature	-40°F to +300°F (-40°C to +149°C)
Reach Compliant (Article 33)	Yes
Certification/Specification	CAGE Code 53421
Package Quantity (Imperial)	150
Package Quantity (Metric)	150
Customs Number	3919102055
Labels per Column	1
Labels per Row	1

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com