

Specification Sheet

Part Number: 558-00416



HellermannTyton inkjet ink dries immediately on these labels to reduce or eliminate smearing.

Polyester material resists a wide range of chemicals and solvents. BS5609 polypropylene available to meet strict marine and maritime labeling requirements.

Can be printed multiple colors, reducing the typical inventory of labels with colored headers and the frequent need to switch stock.

Inkjet Continuous Roll, 4" x 125', White, Polyester, 125'/roll

Article Number	558-00416
----------------	-----------

Type	HT4WTP101125
------	--------------

Color	White (WH)
-------	------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton inkjet label rolls provide flexible options for creating full-color, chemical-resistant safety, warning and arc-flash labels. They are available on continuous rolls of 125' in 1" to 4" widths or die-cut shapes. TagPrint® Pro software contains many common pre-saved safety label designs for easy editing. Save time and money compared to buying online, and no minimums to worry about.
---------------------	--

Short Description	Inkjet Continuous Roll, 4" x 125', White, Polyester, 125'/roll
-------------------	--

Global Part Name	HT4WTP101125-PET-WH
Length L (Imperial)	125
Width W (Imperial)	4.0
Width W (Metric)	101.6
Thickness T (Imperial)	.007
Thickness T (Metric)	64.0
Width of Liner (Metric)	101.6
Width of Liner (Imperial)	4.0
Material	Polyester (PET)
Material Shortcut	PET
Adhesive	Acrylic
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Adhesive Operating Temperature	-40°F to +300°F (-40°C to +149°C)

Operating Temperature	-40°F to +300°F (-40°C to +149°C)
Reach Compliant (Article 33)	Yes
Certification/Specification	CAGE Code 53421
Package Quantity (Imperial)	125
Package Quantity (Metric)	38.1
Customs Number	3919102055
Labels per Column	1
Labels per Row	1

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com