

Specification Sheet

Part Number: 514REF

- Compact to easily fit in a pocket or on a tool belt.
- Dispenser can be reloaded over and over, making it cost effective to use.
- Dispenser edge allows easy removal of label liner.
- Unlike masking tape, dispenser protects labels from dirt and moisture before use, extending the life and quality of the labels.



Rite-On Self-Laminating Label Refill, 0.75" x .38" x 1.25", VL, White, 200/roll

Article Number	590-05141
Type	514REF
Color	White (WH)
Quantity Per	pack
Product Description	HellermannTyton's Rite-On Markers are self laminating wire and cable labels made of flexible vinyl film. A built in clear tail seals the imprint under clear vinyl, maintaining the quality of the messaging and the labels. Rite-On Markers are packaged in a reusable dispenser made from high impact plastic that is resistant to oils and grease.
Short Description	Rite-On Self-Laminating Label Refill, 0.75" x .38" x 1.25", VL, White, 200/roll

Global Part Name	514REF-100B-WH
------------------	----------------

Fixation Method	Pasting / Stick
-----------------	-----------------

Variant	Roller form
---------	-------------

Width W (Imperial)	0.75
--------------------	------

Width W (Metric)	19.05
------------------	-------

Bundle Diameter Min (Imperial)	0.15
--------------------------------	------

Bundle Diameter Min (Metric)	3.89
------------------------------	------

Bundle Diameter Max (Imperial)	0.26
--------------------------------	------

Bundle Diameter Max (Metric)	6.68
------------------------------	------

Height H (Imperial)	0.375
---------------------	-------

Height H (Metric)	9.50
-------------------	------

Outside Diameter Max (Imperial)	0.263
---------------------------------	-------

Outside Diameter Min (Metric)	3.89
-------------------------------	------

Outside Diameter Min (Imperial)	0.153
---------------------------------	-------

Outside Diameter Max (Metric)	6.68
-------------------------------	------

Material	Type 100B, Vinyl, white transparent, self-laminating (100B)
Material Shortcut	100B
Adhesive	Acrylic
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Adhesive Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	200
Package Quantity (Metric)	200
Customs Number	3919102055

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)