

Specification Sheet

Part Number: 596-00663

Made with UV-stable inks and materials for durability and weather resistance.

Reflective properties to meet applicable NEC code requirements for reflective identification.

Supplied with an aggressive adhesive to ensure long life.

Meets NEC & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.



Solar Label, WARNING GROUNDED CONDUCTORS ENERGIZED..., 4.12" x 2.0", VL, Orange, 10/pkg

Article Number	596-00663
Type	WGCME10
Color	Orange (OG)
Quantity Per	pack

Product Description	HellermannTyton makes it easier than ever for solar installers to meet PV labeling codes. Solar Label Convenience Packs allow installers to quickly and economically purchase high quality preprinted NEC code-compliant solar installation labels. Packaged in 10-count quantities to meet the needs of smaller scale solar installations and independent contractors, Solar Label Convenience Packs are available in HellermannTyton's most popular preprinted NEC code-compliant solar label formats. Each Solar Label Convenience Pack contains 10 solar installation labels. Choose from a variety of regular and reflective preprinted labels. For enhanced durability, clear laminate overlay labels are also available in a convenience pack.
Short Description	Solar Label, WARNING GROUNDED CONDUCTORS ENERGIZED..., 4.12" x 2.0", VL, Orange, 10/pkg
Global Part Name	WGCME10-443/281-OG
Local Order Number 2	Cross Reference = 50 per roll: 596-00498; Metal Solar Placard 5 pack: 596-00830
Width W (Imperial)	4.12
Width W (Metric)	104.65
Thickness T (Imperial)	0.0025
Thickness T (Metric)	64.0
Height H (Imperial)	2.0
Height H (Metric)	50.8

Material	Type 443/281, UV stabilized, flexible white vinyl with clear polyester laminate (443/281)
Material Shortcut	443/281
Adhesive	Acrylic
Halogen Free	No
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Adhesive Operating Temperature	-40°F to +174°F (-40°C to +79°C)
Operating Temperature	-40°F to +174°F (-40°C to +79°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL 969 NEC2014
Warranty (US)	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	10
Package Quantity (Metric)	10
Customs Number	3919905060

Labels per Column 1

Labels per Row 1

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)