

Specification Sheet

Part Number: TCWM15

Handi-Paks booklets fit in a pocket for easy transport and access.

A single marker can be removed at the top of each label so that the terminal block can be marked and the remaining label can be used to mark the associated wire connected to the terminal.

Markers are kitted on each page so that any marker can be removed without affecting the other markers on the page.

Markers have a micro-perforation in the middle of each marker so that they can be broken into two pieces for use on small gauge wires, eliminating waste and reducing costs.



Handi-Pak Marker Booklet, (10) 46–90, White, 1/pkg

Article Number	598-00274
Type	TCWM15
Color	White (WH)
Quantity Per	pack
Product Description	Handi-Pak Marker Booklets are convenient pocket sized books that contain pages of black, pre-printed legends on a white background. The legends are printed on a plastic coated cloth label that remains flexible for use in identifying wires and cables. A strong adhesive assures long lasting identification on small wires, cables or anything requiring permanent or temporary identification.

Short Description	Handi-Pak Marker Booklet, (10) 46–90, White, 1/pkg
-------------------	--

Global Part Name	TCWM15-TYHC-WH
------------------	----------------

Length L (Imperial)	1.625
---------------------	-------

Length L (Metric)	41.27
-------------------	-------

Width W (Imperial)	0.25
--------------------	------

Width W (Metric)	6.35
------------------	------

Bundle Diameter Min (Imperial)	0.13
--------------------------------	------

Bundle Diameter Min (Metric)	3.40
------------------------------	------

Bundle Diameter Max (Imperial)	0.3
--------------------------------	-----

Bundle Diameter Max (Metric)	7.50
------------------------------	------

Height H (Imperial)	1.5
---------------------	-----

Height H (Metric)	38.1
-------------------	------

Outside Diameter Max (Imperial)	0.375
---------------------------------	-------

Outside Diameter Min (Metric)	2.54
-------------------------------	------

Outside Diameter Min (Imperial)	0.1
---------------------------------	-----

Outside Diameter Max (Metric)	9.52
-------------------------------	------

Material	Vinyl Cloth (TYHC)
Material Shortcut	TYHC
Adhesive	Rubber
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Adhesive Operating Temperature	-40°F to +248°F (-40°C to +120°C)
Operating Temperature	-40°F to +248°F (-40°C to +120°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	3919905060
Labels per Column	15
Labels per Row	3

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)