

Specification Sheet

Part Number: GT.50X60C2W



Features quick release for repetitive access to cable and wire.

Can be opened and closed numerous times without failure.

Adjustable so one size can accommodate multiple bundle sizes.

Grip Tie with White Write-On Area, 6.0" x .5", PA6/PP, Black, 100/pkg

Article Number	854-44338
----------------	-----------

Type	GT.50X6W
------	----------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	In situations where instant identification is needed, HellermannTyton provides Grip Ties with a white write-on area. This smudge-free surface is ideal for fast and easy identification with a ballpoint pen or felt-tip marker. The write-on area is approximately 3/8"H x 1-1/4"W. It is positioned in the center of the black 6", 8", and 11" straps, as well as spaced every 12" on the Grip Tie rolls.
---------------------	---

Short Description	Grip Tie with White Write-On Area, 6.0" x .5", PA6/PP, Black, 100/pkg
-------------------	---

Global Part Name	GT.50X6W
------------------	----------

Minimum Tensile Strength (Imperial)	40
Minimum Tensile Strength (Metric)	177.93
Length L (Imperial)	6.0
Length L (Metric)	152.4
Width W (Imperial)	0.5
Width W (Metric)	12.7
Bundle Diameter Max (Imperial)	1
Bundle Diameter Max (Metric)	25.4
Material	Polyamide 6 (PA6) Polyethylene (PE)
Material Shortcut	PE PA6
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Reach Compliant (Article 33)	No
Package Quantity (Imperial)	100

Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)