

Specification Sheet

Part Number: GT.50X6MP2V2



Features quick release for repetitive access to cable and wire.

Can be opened and closed numerous times without failure.

Adjustable so one size can accommodate multiple bundle sizes.

Grip Tie, 0.5" x 6.0", PA6/PP, Maroon, 10/pkg

Article Number

854-44352

Type

GT.50X6

Color

Red Brown (RDBN)

Quantity Per

pack

Product Description

The Grip Tie is a low profile, one piece fastening device. Constructed of a hook and loop design, laminated back to back, the Grip Tie features quick release for repetitive access to cable and wire. Grip Ties are available in a variety of colors and are versatile enough for applications ranging from network installations to bundling power cords.

Short Description

Grip Tie, 0.5" x 6.0", PA6/PP, Maroon, 10/pkg

Global Part Name

GT.50X6

Minimum Tensile Strength (Imperial)	40
Minimum Tensile Strength (Metric)	177.93
Length L (Imperial)	6.0
Length L (Metric)	152.4
Width W (Imperial)	0.5
Width W (Metric)	12.7
Bundle Diameter Max (Imperial)	1
Bundle Diameter Max (Metric)	25.4

Material	Polyamide 6 (PA6) Polypropylene (PP)
----------	--------------------------------------

Material Shortcut	PA6 PP
-------------------	--------

UV Resistant (Yes/No)	No
-----------------------	----

Use Conditions	For Indoor Use Only
----------------	---------------------

Plenum Rating	AH-2
---------------	------

Reach Compliant (Article 33)	No
------------------------------	----

UL Recognized (US)	Yes
--------------------	-----

UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	10
Package Quantity (Metric)	10
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)