

Specification Sheet

Part Number: ETST668



PVC Tape is ideal for general purpose electrical applications.

Economical way to splice, terminate and insulate wire and cables.

Meets Mil-Std. MIL-1-7798-A.

Electrical Tape, 0.75" x 66' Roll, 7.0 mil Thick, PVC, Gray, 10 rolls/pkg

Article Number	904-00026
Type	ETST66
Color	Gray (GY)
Quantity Per	pack
Product Description	PVC electrical tape provides fast and easy color coding, cable splicing, terminating, and wire insulating. These comformable high quality tapes have exceptional surface and adhesive characteristics. Tape is applied by overlapping each layer 50% and using tension. After the tape is adhered, the memory of the tape returns, tightening the seal and making the taped area even more waterproof.
Short Description	Electrical Tape, 0.75" x 66' Roll, 7.0 mil Thick, PVC, Gray, 10 rolls/pkg
Global Part Name	ETST66-PVC-GY

Minimum Tensile Strength (Imperial)	15.4
Minimum Tensile Strength (Metric)	68.5
Length L (Imperial)	66.0
Length L (Metric)	20.12
Width W (Imperial)	0.75
Width W (Metric)	19.05
Thickness T (Imperial)	7.0
Material	Flexible Polyvinyl Chloride (PVC)
Material Shortcut	PVC
US MIL SPEC	MIL-1-7798-A
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	+20°F to 176°F (-7°C to +80°C)
Reach Compliant (Article 33)	No
UL Listed (US)	Yes

Package Quantity (Imperial)	10
Package Quantity (Metric)	10
Customs Number	3919102020

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)