


SPECIFICATION FOR APPROVAL




TO: _____

PART NO.		REV.		DELTA SAMPLE ISSUE NO	
PART NAME	EMI FILTER			DELTA MODEL	01MK4
ORDER P/N.	01MK4			SAMPLE ISSUE DATE	

1. PHYSICAL DIMENSIONS:



2. SCHEMATIC:



L: 10.0mH
C1: 0.1uF
C2: 2200pF

REPORT BY	CHECKED BY	APPROVED BY	UNLESS OTHERWISE SPECIFIED DIMENSION TOLERANCE DECIMALS .X± .XX± ANGLES±		
			REV.	99.11.04	

DELTA ELECTRONICS, INC.

8TH FL ASIA ENTERPRISE CENTER 144, SEC. 3 MIN.CHUAN E. ROAD
TAIPEI 10464, TAIWAN. R.O.C.

TELEX 26524 "DELTATRO"
CABLE ADDRESS: "DELTATRO" TAIPEI
TEL: (02) 7164822, 7167790
"DELTATRO" TAIPEI

SPECIFICATION FOR APPROVAL



TO: _____

PART NO.		REV.		DELTA SAMPLE ISSUE NO	
PART NAME	EMI FILTER			DELTA MODEL	01MK4
ORDER P/N.	01MK4			SAMPLE ISSUE DATE	

3. ELECTRICAL CHARACTERISTICS:

3-1. VOLTAGE RATING 115/250VAC

3-2. CURRENT RATING

A. AT 115VAC 1 A RMS Max.

B. AT 250VAC 1 A RMS Max.

3-3. OPERATING FREQUENCY..... 50/60 Hz

3-4. LEAKAGE CURRENT: EACH LINE TO GROUND

A. @115VAC 60Hz 0.20 mA Max.

B. @250VAC 50Hz 0.40 mA Max.

3-5. HIPOT RATING (FOR ONE MINUTE)

A. LINE TO GROUND 2250VDC

B. LINE TO LINE 1450VDC

3-6. TEMPERATURE RANGE: -25 TO +85 DEGREE C

3-7. MINIMUM INSERTION LOSS IN dB: (AT 50 OHM SYSTEM)

FREQ. MHz	.01	.05	.10	.15	.50	1.0	5.0	10	30
COM. MODE dB	10	15	25	30	50	40	40	35	20
DIF. MODE dB	0	0	3	5	25	40	40	40	20

3-8. SAFETY



REV.	2. 01.04.23	
	1. 99.11.04	

DELTA ELECTRONICS, INC.

9TH FL ASIA ENTERPRISE CENTER 144, SEC. 3 MIN.CHUAN E. ROAD
TAIPEI 10464, TAIWAN. R.O.C.

TELEX 26524 "DELTATRO"
CABLE ADDRESS: "DELTATRO" TAIPEI
TEL: (02) 7164822, 7167790
"DELTATRO" TAIPEI