



colour	pinning side A
brown	1
white	2
blue	3
black	4

All dimensions are in mm

**Product properties**

Standard	DIN EN 61076-2-101
Product type	Sensor actuator cable
Connector	M15S101-1M03-YY-04 (see connector data sheet)
Shielding	360°
Number of contacts	4 x male
Thread type	M12
Coding	A-standard, D
Standard length (A)	0,3m - 0,5m - 1,0m - 1,5m - 2,0m - 2,5m - 3,0m - 5,0m - 10,0m

**Cable data**

Type	LIF9Y-C11Y
Specification	UL 758/1581 FT2
Core	4 x 0,34 mm <sup>2</sup>
Core colours	brown, white, blue, black
Jacket	PUR, black
Other	suitable for drag chain

**Packaging**

Standard	bag
----------	-----

**Coding**

coding	LM03-001-XXX-YY-ZZ	
	-A0	-D0
-YY		

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

For the installation of the electrotechnical equipment, particular electrotechnical expertise is required.



Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
F. Wein	16.07.24	F. Wein	20.11.24	500	24-v372	A. Streibl	20.11.24