

## M8Cab-3-F-WE-M/M8Cab-4-F-WE-M

M8 female moulded Connector with wire ends.



IP67 M8 straight moulded 3 or 4 position A coded connector with wire ends and a 1metre cable. Designed for Sensors, actuators, and industrial controllers. 8mm threaded joint, quick easy mating and locking, even in places difficult to reach. Antivibration locking design.

Rated Current: 4A.
Rated Voltage: 60V.

Connector mounting: Rear fastened.

Mechanical Operation: >500 mating cycles.

Ingress Protection: IP67/IP68. Insulation Resistance:  $\geq$ 100M $\Omega$ . Contact Resistance:  $\leq$ 5m $\Omega$ .

Contact Resistance. 251117.

Operating Temperature: -20°C to 80°C.

## **Materials and Coatings:**

Contact Pin: Brass with gold plated.

Contact Termination: Wire end 1m cable length.

O-ring Seal: Epoxy resin/FKM. Hex Nut: Brass with nickel plated.


Screw Thread: M8X1.

Standard: IEC 61076-2-104

Weight: 60g



## Dimensions in mm:





## **Ordering information**

Name	Description	Order Code
M8Cab-3-F-WE-M	M8 3 pin female circular moulded wire end connector	M8Cab-3-F-WE-M
M8Cab-4-F-WE-M	M8 4 pin female circular moulded wire end connector	M8Cab-4-F-WE-M
Date		Notes
02 May 2024	Document version: v1.0	Initial Release







