

M8Con-3-F-SC-F/M8Con-4-F-SC-F

M8 Female Panel mounted Connector Solder Type Front Fastened



3 position female connector

IP67 M8 straight shielded PCB Panel Mount 3 or 4 pin A coded connector. Designed for Sensors, actuators, and industrial controllers. 8mm threaded joint, quick easy mating and locking, even in places difficult to reach. Anti-vibration locking design.

Rated Current: 4A. Rated Voltage: 60V.

Connector mounting: Front fastened.

Mechanical Operation: >500 mating cycles.

Ingress Protection: IP67/IP68. Insulation Resistance: ≥100MΩ.

Contact Resistance: $\leq 5m\Omega$.

Operating Temperature: -20°C to 80°C.

Materials and Coatings:

Contact Pin: Brass with gold plated.
Contact Termination: Solder cup.
O-ring Seal: Epoxy resin/FKM.
Hex Nut: Brass with nickel plated.

Screw Thread: M8X1.


Standard: IEC 61076-2-104





4 position female connector

Dimensions in mm:



Ordering information

Name	Description	Order Code
M8Con-3-F-SC-F	M8 3 pin female circular panel mount connector	M8Con-3-F-SC-F
M8Con-4-F-SC-F	M8 4 pin female circular panel mount connector	M8Con-4-F-SC-F
Date		Notes
08 May 2024	Document version: v1.0	Initial Release







