

PPC-F17D-ULT5

17" 8th gen Intel® Whiskey Lake-U Industrial Panel PC



Features

- » 17" Panel PC with 8th gen Intel® Whiskey Lake-U processors
- » Low power consumption and fanless design
- » IP66-rated front panel for water and dust resistance
- » Touch screen with anti-UV / anti-glare coating
- » Support PoE PD power
- » Support NVMe SSD

Specifications

Display	
LCD Size	17"
Brightness(cd/m2)	350
Max Resolution	1280 x 1024
Contrast Ratio	1000:1
Backlight MTBF(hrs)	50000
System	
Cooling method / System Fan	Fanless
CPU	8th Generation Intel® Core™ i5-8365U 4.10GHz
	8th Generation Intel® Celeron® 4305U 2.20GHz
Chipset	Intel® Whiskey Lake-U
Memory Ext.	2 x 260-pin 2400 MHz dual-channel DDR4 unbuffered SO-DIMM
Memory Max.	32GB
Storage	2.5" HDD/SSD SATA 3(6.0Gb/s) bay
I/O Interface	
Ethernet	2x Intel® I211
	1x Intel® I219
Audio Codec	ALC888S
Power	
Input	+12VDC
Power adapter	12V @ 8A(96W)
Power consumption	66W
Environment	
Operating Temperature	-10°C ~ 50°C (with air flow)
Operating Vibration	5~17Hz, 0.1 double amplitude displacement 17~640Hz 1.5G acceleration peak to peak
Operating Shock	10G acceleration part to part (11ms)
Safety & EMC	CE, FCC
Humidity	10% ~ 95% (non-condensing)
Storage Temperature	-20°C ~ 60°C

IP Level	Front panel IP66
Physical Characteristics	
Color	PANTONE 296 C
Mounting	Wall mount, Panel mount, Rack mount
Dimensions (LxWxH) (mm)	408.4 x 341.4 x 75.6
Net Weight	6.7kg
Construction Front Panel	Aluminum
Cutout Dimensions	391 x 324
Expansion Slots	
Expansion Slots	M.2 2230 A-Key(PCIe x1, USB 2.0; support Wi-Fi, BT)
	M.2 2280 M-Key(PCIe x4; support NVMe SSD)
LCD	
LCD Color	16.7M
Pixel Pitch (mm)	0.26 x 0.26
Viewing Angle (H-V)	170°/160°
Touch	
Touch Screen	PCAP 10-point
Touch Controller	EETI
Other Features	
TPM	TPM 2.0(on-board)
I/O Interface	
I/O Interface	1 x AT/ATX Switch
	1 x Clear CMOS
	1 x Power Switch (with LDE(Blue))
	1 x Line out
	2 x RS-232 (1 x RS-232/422/485, 1 x RS-232)
	1 x HDMI™
	3 x LAN (2 x Support PoE(IEEE 802.3at/bt, optional))
	1 x DC Input Jack (12V Din 4Pin/lock)
	1 x Reset Button
	4 x USB 3.2 Gen2x1

Ordering Information

PPC-F17D-ULT5-i5/4G/PC-R10	17" 350 cd/m2 1280 x 1024 Panel PC with Intel® 14nm 8th Whiskey Lake Core- i5-8365UE (6M Cache, up to 4.10 GHz) TDP 15W on-board Processor (ULT), 4GB DDR4 RAM x1, 12VDC input, Projective capacitive touch window with AG, R10
----------------------------	---

Packing List

1 x PPC-F17D-ULT5 panel PC	1 x Power adapter
1 x Power cord	4 x Screws (M4*8) for VESA mounting
4 x Screws (M3*4) for HDD installation	