











RECOMMENDED
FRONT MOUNTING CUT-OUT





RECOMMENDED
REAR MOUNTING CUT-OUT



NOTES:

1. MEETS IEC 60320 SPECIFICATION
2. AGENCY IDENTIFICATION & RATING:
UL & CSA: 15A, 250V~ AC
VDE: 10A, 250V AC
3. MATERIALS:
HOUSING: BLACK POLYESTER
PINS: TIN PLATED COPPER ALLOY
4. THIS PRODUCT IS RoHS COMPLIANT.



CUSTOMER DRAWING

					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.				
					SIZE	WIDTH	MULT	LBS/M	TEMPER
					FINISH SPEC No.				MATERIAL SPEC No.
					FIRST USED ON		SCALE 2:1		
					DATE DRAWN	BY	CHKD	APVD	Switchcraft®
					11/17/11	BL	BL	TJK	
					NAME MALE AC RECEPTACLE SOLDER TERMINALS, RoHS				PART No. EAC301X
					DO NOT SCALE DRAWING				REV C
REVISIONS									
C	28549	01-16-23	PC	TJK					
B	28323	10-01-20	PC	TJK					
A	27299	5-30-14	TO	TJK					
REV	ECO NUMBER	DATE	BY	APVD					