





NOTES:

1. DIMENSIONS IN MILLIMETERS [INCHES].
2. TAPE CONFORMS TO ANSI/EIA-481.
3. MAXIMUM COMPONENT ROTATION WITHIN CAVITY 20°.
4. REEL SIZE 15 INCH, PLASTIC
5. PART QUANTITY PER REEL: 200
6. ALL DIMENSIONS ARE REFERENCE
7. THIS PRODUCT IS RoHS COMPLIANT

PART NUMBER	PART REV.	POWER JACK
RASM712PTRP15X	A	RASM712PX
RASM722PTRP15X	A	RASM722PX
RASM732PTRP15X	A	RASM732PX

CUSTOMER DRAWING

					★ STAR SYMBOL DENOTES CRITICAL DIMENSION UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES -TWO PLACE DECIMALS ±0.01 -THREE PLACE DECIMALS ±0.005 -ANGLES ±1° -ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R. 2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±0.002 3. REMOVE ALL BURRS DO NOT SCALE DRAWING	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.						
						SIZE	WIDTH		MULT	LBS/M	TEMPER	
						FINISH SPEC No.				MATERIAL SPEC No.		
						FIRST USED ON			SCALE 3:10		Switchcraft® SHEET OF	
						DATE DRAWN	BY	CHKD	APVD			
A	25129	9-2-05	JL	MW	01-Sep-05	JL	MW 9-1-05	MW 9-1-05				
REV	ECO NUMBER	DATE	BY	APVD	NAME RA POWER JACK WITH POST TAPE & REEL 15", RoHS					PART No. RASM7_2PTRP15X		REV A
REVISIONS												