

COAXIAL CONNECTOR, MMCX, 50 Ohm, Right angle cable plug (male)

16_MMCX-50-2-1/111_O

Properties

- Very small size
- Easy to connect and disconnect
- Wide range of board connectors and cable connectors available



Product configuration		
Interface type	Gender	Standard
MMCX	plug	HUBER+SUHNER-MMCX
Interface and material data		
Piece parts	Material	Plating
Centre contact	Bronze	Gold Plating (Nickel underplated)
Outer conductor	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	
Electrical data		
Impedance	50 Ω	
Interface frequency	6 GHz	
Mechanical data		
Weight	0.0006 kg	
Mating cycles	500	
Cable entry centre contact	soldered	
Cable entry outer contact	soldered	
Environmental data		
Operation temperature	-55 °C ... 155 °C	

COAXIAL CONNECTOR, MMCX, 50 Ohm, Right angle cable plug (male)
16_MMCX-50-2-1/111_O

Ordering Information Table		
Item number	Item description	Packaging type
22645957	16_MMCX-50-2-1/111_OE	Single
22649044	16_MMCX-50-2-1/111_OH	Bulk 100 pcs

Suitable cables	
Cable group	Y3 - 2 mm / 50 Ohm
	Y16 - 2 mm / 50 Ohm
	Y11 - 2 mm / 50 Ohm
Suitable cables	SR_86_TP_M17

Additional Information	
Only as assembly	No

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3112 / Date of publication: 11.04.2024 / uncontrolled copy