

COAXIAL CONNECTOR, MMBX, 50 Ohm, Straight bulkhead receptacle, jack (female)

22_MMBX-50-0-2/111_N

Properties

- Smallest board-to-board distance
- Very high frequencies
- Excellent return loss values
- Blind mateable
- Reliable and secure connection



Product configuration

Interface type	Gender	Standard
MMBX	jack	HUBER+SUHNER-MMBX

Interface and material data

Piece parts	Material	Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PTFE / LCP	

Electrical data

Impedance	50 Ω
Interface frequency	12.4 GHz

Mechanical data

Weight	0.0011 kg
Mating cycles	100
Flange type	round flange / dia. 10
Tab style	PIN

Environmental data

Operation temperature	-55 °C ... 155°C
-----------------------	------------------

Ordering Information Table

Item number	Item description	Packaging type
84005177	22_MMBX-50-0-2/111_NY	Tray

COAXIAL CONNECTOR, MMBX, 50 Ohm, Straight bulkhead receptacle, jack (female)
22_MMBX-50-0-2/111_N

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2800 / Date of publication: 26.11.2023 / uncontrolled copy