

**COAXIAL CONNECTOR, BNC, 50 Ohm, Straight cable plug (male)**

11\_BNC-50-1-9/133\_N

**Properties**

- Useful for frequently coupled and uncoupled connections
- Available for 50 ohm and 75 ohm applications
- Applicable in frequencies up to 4 GHz

**Product configuration**

|                |        |                                         |
|----------------|--------|-----------------------------------------|
| Interface type | Gender | Standard                                |
| BNC            | plug   | IEC 60169-8_MIL-STD-348A/301_CECC 22120 |

**Interface and material data**

|                 |                       |                                   |
|-----------------|-----------------------|-----------------------------------|
| Piece parts     | Material              | Plating                           |
| Centre contact  | Brass                 | Gold Plating (Nickel underplated) |
| Outer conductor | Brass                 | SUCOPLATE (R) Plating             |
| Body            | Brass                 | SUCOPLATE (R) Plating             |
| Insulator       | PFA / PTFE            |                                   |
| Coupling nut    | Brass                 | SUCOPLATE (R) Plating             |
| Gasket          | VMQ (Silicone rubber) |                                   |

**Electrical data**

|                     |             |
|---------------------|-------------|
| Impedance           | 50 $\Omega$ |
| Interface frequency | 4 GHz       |

**Mechanical data**

|                            |           |
|----------------------------|-----------|
| Weight                     | 0.0151 kg |
| Mating cycles              | 500       |
| Cable entry centre contact | soldered  |
| Cable entry outer contact  | clamped   |

**Environmental data**

|                       |                   |
|-----------------------|-------------------|
| Operation temperature | -65 °C ... 165 °C |
|-----------------------|-------------------|

**COAXIAL CONNECTOR, BNC, 50 Ohm, Straight cable plug (male)**

11\_BNC-50-1-9/133\_N

| Material compliance |                                   |                                 |                      |
|---------------------|-----------------------------------|---------------------------------|----------------------|
| Item number         | Directive / Regulation            | Rating                          | Exemptions / Details |
| 22642296            | RoHS 2011/65/EU and (EU) 2015/863 | Compliant with exemption        | 6c                   |
|                     | REACH 1907/2006 Article 33 SVHC   | Contains one or more SVHC >0,1% | CAS: 7439-92-1 Lead  |

| Ordering Information Table |                      |                |
|----------------------------|----------------------|----------------|
| Item number                | Item description     | Packaging type |
| 22642296                   | 11_BNC-50-1-9/133_NE | Single         |

| Suitable cables   |                         |
|-------------------|-------------------------|
| Cable group       | U99 - Customer specific |
| Additional cables | spez.Cable              |

| Additional Information |    |
|------------------------|----|
| Only as assembly       | No |

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.  
DOCUMENT PIM-P3708 / Date of publication: 12.07.2025 / uncontrolled copy