


COAXIAL CONNECTOR, SMA-26.5GHz, 50 Ohm, Straight cable plug (male)

11_SMA-50-2-100/111_N

Properties

- Excellent return loss
- Intermateable with PC3.5 and SK
- Applicable in frequencies up to 18 GHz



Product configuration

Interface type	Gender	Standard
SMA-26.5GHz	plug	HUBER+SUHNER-SMA-26.5GHz

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Bronze	Gold Plating (Nickel underplated)
Gasket	VMQ (Silicone rubber)	

Electrical data

Impedance	50 Ω
Interface frequency	26.5 GHz

Mechanical data

Weight	0.0031 kg
Mating cycles	500
Cable entry centre contact	soldered
Cable entry outer contact	soldered

Environmental data

Operation temperature	-65 °C ... 165 °C
-----------------------	-------------------

COAXIAL CONNECTOR, SMA-26.5GHz, 50 Ohm, Straight cable plug (male)

11_SMA-50-2-100/111_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22648717	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22648717	11_SMA-50-2-100/111_NE	Single

Suitable cables	
Cable group	Y3 - 2 mm / 50 Ohm
	Y16 - 2 mm / 50 Ohm
Suitable cables	SUCOFORM_86
	SR_86_TP_M17

Additional Information	
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22544715	74_Z-0-0-68	Knives / Blades
22544559	74_Z-0-0-60	Support
22544558	74_Z-0-0-59	Support
22544557	74_Z-0-0-58	Assembly tool
22544555	74_Z-0-0-54	Holders
23024588	74_Z-0-0-442	Soldering tool
22648865	74_Z-0-0-281	Trimming tool
22648904	74_Z-0-0-263	Gauges
22648903	74_Z-0-0-262	Gauges
22645823	74_Z-0-0-224	Positioning aids
22643028	74_Z-0-0-164	Trimming tool
22643029	74_Z-0-0-157	Cable stripping tool
23019269	74_Z-0-0-365	Support
23021266	74_Z-0-0-369	Locator

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3486 / Date of publication: 12.07.2025 / uncontrolled copy