

SENCITY® Spot-M SISO WiFi Antenna

1324.17.0051

Properties

- Directional high gain antenna for Wi-Fi 1/Wi-Fi 3 bands
- Supports from 2.3 GHz to 2.7 GHz frequency bands
- Half power beamwidth of 32° (vertical) and 32° (Horizontal)
- For both indoor and outdoor mounting with IP rating IP67
- Integrated N female interface



Electrical data			
	Band 1	Band 2	Band 3
Frequency	2300 MHz ... 2400 MHz	2400 MHz ... 2500 MHz	2500 MHz ... 2700 MHz
Impedance	50 Ω	50 Ω	50 Ω
VSWR	1.9	1.9	1.9
Gain	14 dBi	14.5 dBi	15 dBi
HPBW vertical	32 °	32 °	32 °
HPBW horizontal	32 °	32 °	32 °
Front to back ratio	26 dB	26 dB	26 dB
Side Lobe Suppression vertical	ETSI EN 301 525 V1.1.1 (2000-06)		
Side Lobe Suppression horizontal	ETSI EN 301 525 V1.1.1 (2000-06)		
Vertical Electrical Tilt	0 °	0 °	0 °
Ambient Temperature	25 °C		
Composite Power max	6 W		

Ports	
	Port 1
Connector	N, jack (female)
Polarization	vertical
DC grounded	Yes

SENCITY® Spot-M SISO WiFi Antenna

1324.17.0051

Mechanical data	
Weight	0.5 kg
Dimensions	190 mm x 190 mm x 30 mm (Height x Width x Depth)
Windload	front: 105 N at 160 km/h, lateral: 16 N at 160 km/h, Wind Speed survival: 220 km/h

Material data	
Radome material	Plastic
Radome colour	RAL 9002 (grey-white)
Back plate/base plate material	Aluminum

Environmental data	
Operation temperature	-45 °C ... 71 °C
Storage temperature	-45 °C ... 71 °C
Transport temperature	-55 °C ... 71 °C
Environment (application)	Indoor/Outdoor
Ingress protection (IP Rating)	IP67
Flammability rating	UL 94-HB

Environmental remarks	
Humidity ETSI EN300-2-4 T4.1E 144h 95% Solar radiation ASTM G53 1000 h Salt spray IEC 60068-2-11 Ka 500 h Mechanical shock IEC 60721-3-4 4M5 Vibration IEC 60721-3-4 30 min/axis random 4M5 Low temperature IEC 60068-2-1 72h -55°C High temperature IEC 60068-2-2 72h +71°C Temperature cycling IEC 60068-2-14 1h -45 to +70°C 3 cycles	

Antenna accessories		
Item description	Item number	Product name
9091.99.0201	84018626	SENCITY Planar Antenna Downtilt Bracket

Ordering information		
Item description	Item number	Product name
1324.17.0051	84018384	SENCITY® Spot-M SISO WiFi Antenna

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
 DOCUMENT PIM-P3312 / Date of publication: 12.08.2025 / uncontrolled copy