

SENCITY® Omni-SR Dome Antenna

1399.17.0108

Properties

- Compact Omnidirectional outdoor antenna for Wi-Fi 6E bands (2.4 GHz / 5GHz / 6 GHz) & industrial 5G (3.7-3.8 GHz)
- Rugged design, meets EN 50155 Railway Standard and IP68 rating
- Fire retardant acc. to DIN 5510-2, BS 6853, NF F16-101/102, EN 45545-2
- Single hole mounting

**Electrical data**

	Band 1	Band 2	Band 3	Band 4
Frequency	2400 MHz ... 2500 MHz	2500 MHz ... 2700 MHz	3400 MHz ... 3800 MHz	4900 MHz ... 5925 MHz
Impedance	50 Ω	50 Ω	50 Ω	50 Ω
VSWR	1.8	2	2	1.8
Gain	6 dBi	6 dBi	6 dBi	8 dBi
Ambient Temperature	25 °C	25 °C	25 °C	25 °C
Composite Power max	350 W	350 W	300 W	300 W

	Band 5
Frequency	5925 MHz ... 7125 MHz
Impedance	50 Ω
VSWR	1.9
Gain	8 dBi
Ambient Temperature	25 °C
Composite Power max	300 W

Electrical remarks

Remarks	Gain measured using a Ø1m ground plane 10dB beamwidth horizontal: 360°
---------	---

Ports

	Port 1
Connector	N, jack (female)
Polarization	vertical
DC grounded	Yes

SENCITY® Omni-SR Dome Antenna

1399.17.0108

Connections	
	Port 1
Band 1	✓
Band 2	✓
Band 3	✓
Band 4	✓
Band 5	✓

Mechanical data	
Weight	0.3 kg
Dimensions	50.6 mm x 86 mm (Height x Diameter)
Windload	front: 10 N at 160km/h, Wind Speed survival: 160 km/h

Material data	
Radome material	ASA (acrylic ester-styrene-acrylonitrile)
Radome colour	RAL 7043 (dark grey)
Back plate/base plate material	Stainless steel

Environmental data	
Operation temperature	-40 °C ... 80 °C
Storage temperature	-40 °C ... 80 °C
Transport temperature	-40 °C ... 80 °C
Environment (application)	Outdoor
Ingress protection (IP Rating)	IP68
Flammability rating	DIN 5510

Environmental remarks	
Vibration test (24 hours) acc. to EN60068-2-64.	
Shock test (35g) acc. to EN60068-2-27.	
Flammability rating DIN 5510-2, BS 6853, NF F16-101/102, EN 45545-2.	

Additional Information	
The antenna 1399.17.0108 can be mounted on a support with a thickness of up to 30mm (Antenna 1399.17.0111: 10mm). Please refer to the mounting instruction for installation details.	

Ordering information		
Item description	Item number	Product name
1399.17.0108	84040934	SENCITY® Omni-SR Dome Antenna

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3269 / Date of publication: 13.08.2025 / uncontrolled copy