

SENCITY® Road Antenna

1399.99.0039

Properties

- Rugged vehicle rooftop multi-band antenna for heavy duty vehicles like bus and truck
- Supports cellular, WiFi 2.4, 5 GHz and IEEE 802.11p, GPS/Glonass.
- Offers a stick antenna socket and separate connector for each application.
- Single hole mounting, easy cabling feed-through
- Works also on non-metallic surfaces.



Electrical data

	Band 1	Band 2	Band 3	Band 4
Name				
Frequency	698 MHz ... 790 MHz	790 MHz ... 960 MHz	1710 MHz ... 2690 MHz	1710 MHz ... 2690 MHz
Impedance	50 Ω	50 Ω	50 Ω	50 Ω
VSWR	2.1	1.8	2	1.8
Gain	5 dBi	5 dBi	4 dBi	6 dBi
Isolation between Ports			20 dB	20 dB
Ambient Temperature	25 °C	25 °C	25 °C	25 °C
Composite Power max	80 W	40 W	40 W	40 W

	Band 5	Band 6	Band 7
Name		GPS/Glonass	Socket
Frequency	4900 MHz ... 5935 MHz	1574 MHz ... 1610 MHz	
Impedance	50 Ω	50 Ω	
VSWR	1.8	2	
Gain	7 dBi		
Isolation between Ports	30 dB		
Ambient Temperature	25 °C		
Composite Power max	30 W		

SENCITY® Road Antenna

1399.99.0039

Electrical remarks	
Remarks	Indicated VSWR values are valid for a metallic ground plane of 0.5 x 0.5m or larger. In the 790-5935 MHz band, indicated VSWR values are also valid for installations on non-metallic surfaces. A W-CDMA 2100 and LTE 2600 2x2 MIMO configuration is supported by using port 1 and 2. In this setup, no stub antenna shall be equipped in order to ensure best MIMO performance. Available stick antennas see section 'Related products'.

Ports				
	Port 1	Port 2	Port 3	Port 4
Port name	(white sleeve)	(blue sleeve)	(black sleeve)	(red sleeve)
Connector	SMA, plug (male)	SMA, jack (female)	TNC, plug (male)	TNC, jack (female)
Cable type	ENVIROFLEX_316_D -AM	ENVIROFLEX_316_D -AM	ENVIROFLEX_316_D -AM	ENVIROFLEX_316_D -AM
Cable length	0.23 m	0.2 m	0.26 m	0.3 m
Polarization	vertical	vertical	circular right	
DC grounded	Yes	No	No	No

Connections				
	Port 1	Port 2	Port 3	Port 4
Port name	(white sleeve)	(blue sleeve)	(black sleeve)	(red sleeve)
Band 1	✓			
Band 2	✓			
Band 3	✓			
Band 4		✓		
Band 5		✓		
Band 6			✓	
Band 7				✓

Electrical data LNA	
LNA is connected to	Port 3
Input voltage	3 V ... 5 V
Current consumption	30 mA
Noise figure	2 dB
Total gain @90° elevation	30 dBic
Remarks	Values for LNA power consumption, noise figure and gain are given for a 5V operating voltage and may differ slightly for a lower voltage

Mechanical data	
Weight	0.41 kg
Dimensions	82 mm x 83 mm x 208 mm (Height x Width x Depth)
Mounting breakthrough	Ø 30 mm
Remarks	Stick antenna max. length = 0.5m

SENCITY® Road Antenna

1399.99.0039

Material data	
Radome material	ASA (acrylic ester-styrene-acrylonitrile)
Radome colour	RAL 7043 (dark grey)
Back plate/base plate material	Aluminium

Environmental data	
Operation temperature	-40 °C ... 85 °C
Storage temperature	-40 °C ... 85 °C
Transport temperature	-40 °C ... 85 °C
Environment (application)	Indoor/Outdoor
Ingress protection (IP Rating)	Mated / IP68, IP69
Flammability rating	ECE-R118
Solar radiation	DIN 75220

Environmental remarks	
ISO 16750:2010 environmental tests	
MIL-F-14072D low corrosion design	
E-Mark	
CE-Mark	

Antenna accessories		
Item description	Item number	Product name
9091.99.0254	85007967	TETRA Stick antenna 410-430 MHz
9091.99.0250	84124410	Metal ground plane foil 0.6x0.6m
9091.99.0248	84112257	TETRA Stick antenna 450-470 MHz
9091.99.0247	84112256	TETRA Stick antenna 380-430 MHz
9091.99.0246	84112255	FM Radio Stick antenna 88-108 MHz

Ordering information		
Item description	Item number	Product name
1399.99.0039	84089087	SENCITY® Road Antenna

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P31254 / Date of publication: 20.08.2025 / uncontrolled copy