

SENCITY® Rail MIMO Low Profile Antenna with Dualband GNSS/LNA

1399.99.0082

Properties

- Railway rooftop antenna for 2G/3G/4G/5G cellular and Wi-Fi 6E bands
- Includes dualband GNSS antenna & integrated LNA covering GPS L1+L2+L5/ Galileo E1+E5a+E5b/BeiDou B1+B2+B3/GLONASS G1+G2
- Rugged design, meets EN 50155 Railway Standard and Fire retardant according to EN 45545-2 and NFPA-130
- High Voltage and High Current protection for use under catenary lines
- Extremely low profile (40mm)



Electrical data				
	Band 1	Band 2	Band 3	Band 4
Name	Cellular/Wi-Fi	Cellular/Wi-Fi	Cellular/Wi-Fi	Cellular/Wi-Fi
Frequency	694 MHz ... 960 MHz	1350 MHz ... 1450 MHz	1450 MHz ... 2700 MHz	3300 MHz ... 4200 MHz
Impedance	50 Ω	50 Ω	50 Ω	50 Ω
VSWR	1.8	1.9	1.6	1.8
Gain	5 dBi	7 dBi	6.5 dBi	7.5 dBi
Isolation between Ports	15 dB	16 dB	20 dB	25 dB
Ambient Temperature	25 °C	25 °C	25 °C	25 °C
Composite Power max	40 W	40 W	40 W	40 W

	Band 5	Band 6	Band 7	Band 8
Name	Cellular/Wi-Fi	Cellular/Wi-Fi	GNSS	GNSS
Frequency	4900 MHz ... 5150 MHz	5150 MHz ... 7125 MHz	1164 MHz ... 1279 MHz	1555 MHz ... 1610 MHz
Impedance	50 Ω	50 Ω	50 Ω	50 Ω
VSWR	1.8	1.8	1.5	1.5
Gain	9 dBi	8 dBi		
Isolation between Ports	25 dB	25 dB		
Ambient Temperature	25 °C	25 °C		
Composite Power max	40 W	40 W		

SENCITY® Rail MIMO Low Profile Antenna with Dualband GNSS/LNA

1399.99.0082

Electrical remarks	
Remarks	Indicated VSWR and gain values are valid for a metallic ground plane of 0.5 x 1 m or larger.

Ports			
	Port 1	Port 2	Port 3
Port name	Cell/Wi-Fi 1	Cell/Wi-Fi 2	GNSS
Connector	N, jack (female)	N, jack (female)	TNC, plug (male)
Cable type	RADOX_RF_316_D	RADOX_RF_316_D	RADOX_RF_316_D
Cable length	0.24 m	0.18 m	0.16 m
Polarization	vertical	vertical	circular right
DC grounded	Yes	Yes	No

Connections			
	Port 1	Port 2	Port 3
Port name	Cell/Wi-Fi 1	Cell/Wi-Fi 2	GNSS
Band 1	✓	✓	
Band 2	✓	✓	
Band 3	✓	✓	
Band 4	✓	✓	
Band 5	✓	✓	
Band 6	✓	✓	
Band 7			✓
Band 8			✓

Electrical data LNA	
LNA is connected to	Port 3
Input voltage	3 V ... 5.5 V
Current consumption	45 mA
Noise figure	2 dB
Total gain @90° elevation	38 dBic
Remarks	Values for LNA power consumption, noise figure and gain are given for a 5V operating voltage and may differ slightly for a lower voltage. This Antenna is compliant with the Radio Equipment Directive 2014/53/EU EMC: EN50121-3-2 (2016)

Mechanical data	
Weight	1.3 kg
Dimensions	40 mm x 108 mm x 474 mm (Height x Width x Depth)
Remarks	High-voltage-protection: no voltage on RF port, if the catenary line touches the antenna (EN 50124-1, 3.8 kVDC, 27.5 kVAC, 1min). High-current-protection: Designed acc. to UIC 533, DC-grounded antenna element protection against lightning and short circuit with catenary lines (EN50388, EN 50122-1, 40kA/0.125sec).

SENCITY® Rail MIMO Low Profile Antenna with Dualband GNSS/LNA

1399.99.0082

Mechanical data	
	Corrosion: Low corrosion design acc. to MIL-DTL-14072(E), 96 hours Salt Spray test. Mounting: Shall be installed in longitudinal position to the wind/driving direction. Suitable for installation on high-speed trains with a maximum speed of 500 km/hr. 4x composite sealing washers included for silicone-free sealing of the mounting screws.

Material data	
Radome material	PC (Polycarbonate)
Radome colour	RAL 7043 (dark grey)
Back plate/base plate material	Aluminum
Back plate/base plate plating	Passivated (Plating)
Back plate/base plate colour	Grey

Environmental data	
Operation temperature	-55 °C ... 85 °C
Storage temperature	-55 °C ... 85 °C
Transport temperature	-55 °C ... 85 °C
Environment (application)	Outdoor
Ingress protection (IP Rating)	IP67, IP69
Flammability rating	EN 45545-2 R24 HL3
Solar radiation	UL 746C, FI

Environmental remarks	
Flammability rating: EN45545-2:2013 + A1:2015, NFPA-130:2017 Tested according to ISO 4589-2:2017, NFX 70-100-1:2006, ISO 5659-2:2011. Environmental tests: EN 50155:2018-05 §13.4.6 EN 60068-2-1:2008-01 Cold temperature test Ab, -55°C, 16h §13.4.5 EN 60068-2-2:2008-01 Dry heat test Be +85°C, 16h §13.4.7 EN 60068-2-30:2006-06 Damp heat cyclic test Db, +25/55°C, 2 cycles §13.4.10 EN 60068-2-11:2000-02 Salt mist test, 96h §13.4.11 EN 61373:2011-04 § 8, Cat. 1B Broadband Random Vibration §13.4.11 EN 61373:2011-04 § 9, Cat. 1B Increased Random Vibration §13.4.11 EN 61373:2011-04 § 10, Cat. 1B Mechanical shock §13.4.12 Ingress Protection EN 60529:2014-09 IP6X, IPX5, IPX6, IPX8, IPX9	

Additional Information	
This product meets the Deutsche Bahn specifications for rolling stock equipment. Protected by Patents: DE202015009331(U1), US10116056(B2), CN106663861B.	

Antenna accessories		
Item description	Item number	Product name
9091.99.0257	85068234	Sencity Rail - M10 sealing washer kit
9091.99.0235	84079030	Sencity Rail antenna grounding kit

Ordering information		
Item description	Item number	Product name
1399.99.0082	85150817	SENCITY® Rail MIMO Low Profile Antenna with Dualband GNSS/LNA

SENCITY® Rail MIMO Low Profile Antenna with Dualband GNSS/LNA

1399.99.0082

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P31250 / Date of publication: 20.08.2025 / uncontrolled copy