

COAXIAL CONNECTOR, MMCX, 50 Ohm, Right angle cable plug (male)

16_MMCX-50-1-1/111_O

Properties

- Very small size
- Easy to connect and disconnect
- Wide range of board connectors and cable connectors available



Product configuration		
Interface type	Gender	Standard
MMCX	plug	HUBER+SUHNER-MMCX

Interface and material data		
Piece parts	Material	Plating
Centre contact	Bronze	Gold Plating (Nickel underplated)
Outer conductor	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	
Crimp ferrule	Brass	Gold Plating (without Nickel underplating)

Electrical data	
Impedance	50 Ω
Interface frequency	6 GHz

Mechanical data	
Weight	0.0007 kg
Mating cycles	500
Cable entry centre contact	soldered
Cable entry outer contact	crimped

Engagement / Disengagement force		
	Engagement	Disengagement
Interface force min		6 N
Interface force max	15 N	15 N

COAXIAL CONNECTOR, MMCX, 50 Ohm, Right angle cable plug (male)

16_MMCX-50-1-1/111_O

Environmental data	
Operation temperature	-55 °C ... 155 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22645955	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
22648762	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22645955	16_MMCX-50-1-1/111_OE	Single
22648762	16_MMCX-50-1-1/111_OH	Bulk 100 pcs

Suitable cables	
Cable group	U1 - 1 mm / 50 Ohm
Suitable cables	RG_196_A/U
	RG_178_B/U

Additional Information	
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22645337	76_Z-0-2-53	Crimping dies
22645880	76_Z-0-0-26	Crimping dies
22645861	74_Z-0-0-225	Coupling and decoupling tool

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3118 / Date of publication: 12.07.2025 / uncontrolled copy