

COAXIAL ADAPTER, SMA, 50 Ohm, T-style, 3 jacks (female)

46\_SMA-50-0-1/111\_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



| Product configuration |               |                                           |
|-----------------------|---------------|-------------------------------------------|
| Interface type        | Gender        | Standard                                  |
| SMA                   | jack (female) | IEC 60169-15_MIL-STD-348A/310_CEECC 22110 |
| SMA                   | jack (female) | IEC 60169-15_MIL-STD-348A/310_CEECC 22110 |

| Interface and material data |                        |                                   |
|-----------------------------|------------------------|-----------------------------------|
| SMA                         |                        |                                   |
| Piece parts                 | Material               | Plating                           |
| Centre contact              | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Outer conductor             | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Body                        | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Insulator                   | PFA / PTFE             |                                   |
| SMA                         |                        |                                   |
| Piece parts                 | Material               | Plating                           |
| Centre contact              | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Outer conductor             | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Body                        | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Insulator                   | PFA / PTFE             |                                   |

| Electrical data     |        |
|---------------------|--------|
| Impedance           | 50 Ω   |
| Interface frequency | 18 GHz |

| Mechanical data |           |
|-----------------|-----------|
| Weight          | 0.0029 kg |
| Mating cycles   | 500       |

**COAXIAL ADAPTER, SMA, 50 Ohm, T-style, 3 jacks (female)**

46\_SMA-50-0-1/111\_N

**Environmental data**

|                       |                   |
|-----------------------|-------------------|
| Operation temperature | -65 °C ... 165 °C |
|-----------------------|-------------------|

**Material compliance**

| Item number | Directive / Regulation            | Rating                          | Exemptions / Details |
|-------------|-----------------------------------|---------------------------------|----------------------|
| 22543357    | RoHS 2011/65/EU and (EU) 2015/863 | Compliant with exemption        | 6c                   |
|             | REACH 1907/2006 Article 33 SVHC   | Contains one or more SVHC >0,1% | CAS: 7439-92-1 Lead  |

**Ordering Information Table**

| Item number | Item description     | Packaging type |
|-------------|----------------------|----------------|
| 22543357    | 46_SMA-50-0-1/111_NE | Single         |

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.

DOCUMENT PIM-P1897 / Date of publication: 12.07.2025 / uncontrolled copy