

Accessories

PROTECTIV CAP, BNC, jack (female)

62_BNC-0-0-1/-33_-H

Properties

- Easy to work with
- Available for plug(male) and jack(female) connectors



General data	
Technology	Radio Frequency
Weight	0.0075 kg
Body material	Brass / SUCOPLATE (R) Plating
Gasket material	VMQ (Silicone rubber)
Operation temperature	165 °C
Remarks	Chain length 60 mm

Ordering Information Table	
Item number	Item description
22648487	62_BNC-0-0-1/-33_-H

Accessories

PROTECTIV CAP, BNC, jack (female)

62_BNC-0-0-1/-33_-H

Catalogue drawing

Accessories

PROTECTIV CAP, BNC, jack (female)

62_BNC-0-0-1/-33_-H

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/
EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for
information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1806 / Date of publication: 16.05.2024 / uncontrolled copy