

COAXIAL CONNECTOR, UHF Twin, X Ohm, Straight cable plug (male)

GDA_072/002_-

Properties

- Mateable with 4 mm banana plugs
- Applicable in frequencies up to 200 MHz

**Product configuration**

Gender

plug

Interface and material data

Piece parts	Material	Plating
Centre contact	Brass	Silver Plating
Outer conductor	Brass	Silver Plating
Body	Brass	Silver Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	Nickel Plating

Electrical data

Interface frequency	0.2 GHz
---------------------	---------

Mechanical data

Weight	0.0241 kg
Mating cycles	100

Environmental data

Operation temperature	-25 °C ... 70 °C
-----------------------	------------------

Material compliance

Item number	Directive / Regulation	Rating	Exemptions / Details
22542877	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

COAXIAL CONNECTOR, UHF Twin, X Ohm, Straight cable plug (male)
GDA_072/002_-

Ordering Information Table		
Item number	Item description	Packaging type
22542877	GDA_072/002_-E	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1058 / Date of publication: 12.07.2025 / uncontrolled copy