

MICON 5, square plunger 14.5 mm, mechanical stop limit, red, GH 9.55 mm



Description


The wide selection of standard plungers in different shapes and colors guarantees a versatile range of applications for the MICON 5 tactile switch.

technical data

> general		direct links
Bezel color	red	> RAFI eCatalog
illuminated	Yes	
Packaging unit	100 pcs.	
Net weight	0.9 g	
Minimum order quantity (MOQ)	100 pcs.	
RoHS compliant	Yes	
REACH compliant	Yes	
Country of origin	DE	
> mounting diameters		
Outside dimension, length	8.7 mm	
Outside dimension, width	14.5 mm	
Outside dimension, height	14.5 mm	
Plunger length L	6.2 mm	
Support height A	3.35 mm	
Total height GH	9.55 mm	


drawings

Dimensioned drawing



System drawing

Structure:
High embossing 0.35 mm
Adhesive thickness 0.15 mm



$$GH=A+L$$

PCB drawing

View without front panel,
foil and screen




Illustration with 4 LED OSRAM LO M676-Q1R1-24

PCB drawing

View without front panel,
foil and screen




Illustration with 4 LED OSRAM LO M676-Q1R1-24