# CUSTOMER PRODUCT SPECIFICATION SHEET

RoHS Compliant

# CABLE 196 RF: RF CABLE ASSEMBLY, MMCX R/A PLUG + SMA STRAIGHT BULKHEAD JACK WITH 0-RING RATED TO IP67/68 + MULTIPLE CABLE SIZES

#### SPECIFICATIONS:


- 1. MMCX RIGHT ANGLE PLUG, P/N: FOR RG178. Ø1.37MM CABLES: RFCT-MMCX003-M78.
- FOR Ø1.13MM LL, Ø1.13MM CABLES: RFCT-MMCX002-M13.
- FOR RG316 CABLE: RFCT-MMCX004-M74.
- 2. COAXIAL CABLE, SEE P/N FOR DETAIL.
- 3. SMA STRAIGHT BULKHEAD JACK WITH 0-RING RATED TO IP67/68, P/N: FOR Ø1.13~RG178CABLE: RFCT-SMA002-F78. FOR RG316 CABLE:
- RFCT-SMA002-F74.

### ENVIRONMENTAL:

- A. BULKHEAD MOUNTED CONNECTOR (RFCT-SMA002-Fxx) TESTED TO THE FOLLOWING SPECIFICATION:
  - i. IP6X DUST TIGHT NO PARTICLE INGRESS.
- ii. IPX7 WATERPROOF FOR 30 MINUTES UP TO 1 METER UNDERWATER.
- iii. IPX8 WATERPROOF FOR 48 HOURS AT 1 METER UNDERWATER.
- iv. IPX8 WATERPROOF FOR 12 HOURS AT 5 METERS UNDERWATER.
- v. PRESSURE TEST 1 BAR FOR 10 SECONDS.

#### NOTES:


- 1. THE ORIENTATION OF CONNECTORS ON DRAWING IS FOR REFERENCE ONLY, IF THE ORDER IS LEFT BLANK THE CONNECTOR WILL NOT HAVE FIXED ORIENTATION.
- 2. FIXED ORIENTATION IS SUGGESTED FOR CABLE LENGTH 50MM TO 100MM. PLEASE SPECIFY THE FIXED ORIENTATIONS FROM THE ORDER CODE (F1. F2. ETC)
- 3. CONTACT GCT IF THE ORIENTATION YOU REQUIRE IS NOT SHOWN.
- 4. WORKING FREQUENCY RANGE: DC-3GHz.
- 5. OPERATING TEMPERATURE: -40°C~+125°C.



# USAGE PRECAUTIONS: CABLES USING 'MICRO' COAX ARE DELICATE:


- (i) HANDLE WITH CARE.
- (ii) DO NOT TWIST; APPLY EXCESSIVE FORCES OR SHARP BENDS TO THE CABLE. DO NOT FORCEFULLY DEFORM WIRES.
- (iii) CONSULT CONNECTOR MANUFACTURER'S DATASHEETS FOR DETAILED NOTES
- ON HANDLING INSTRUCTIONS.







11.4 FLAT 5.85



SMA DETAIL DRAWING

"L" LENGTH IN MM:

eg: 100MM = 0100

(MIN. 0050-MAX.2000

STANDARD = 0100, 0150, 0200)

Tolerance: <50mm: ±2mm.

51-200mm: ±5mm. 201-500mm: ±7mm.

>501mm: ±10mm.

## CABLE SIZE OPTIONS:

1 = RG178 CABLE, COLOR: BROWN.

 $2 = \phi 1.13MM LOW LOSS CABLE, COLOR: GRAY.$ 

 $3 = \phi 1.37MM$  CABLE, COLOR: BLACK.

 $4 = \phi 1.13MM$  CABLE, COLOR: GRAY.

5 = RG316 CABLE, COLOR: BROWN.

## WASHER AND NUT OPTIONS:

BLANK = SEPARATELY PACKED (STANDARD)

A = ALL ASSEMBLED WITH CONNECTOR

## ORIENTATION OPTIONS:

BLANK = DOES NOT HAVE A FIXED ORIENTATION

F1 = MMCX CONNECTION DOWN (L=50-200MM)

F2 = MMCX CONNECTION UP (L=50-200MM)
(SEE NOTES 1, 2, 3 AND DIAGRAMS FOR MORE INFORMATION)

IP RATED EVEN WHEN UNMATED

	Scale:	NTS	THIRD ANGLE	Unstated Tolerances: .X N/A .XX N/A	
	Drawn:	KY	ф ф	- XXX N/A ANGLES N/A	١,
	App'd:	XXX	Title CABLE ASSEMBLY		
	Date:	16 FEB. '25	Revision: 2.0	Unit: mm	

IP Rated RF Products



CABLE 196 RF

Type: Cable 196 RF

www.gct.co www.gradconn.com

( ) THIS DRAWING IS CONFIDENTIAL AND MUST NOT BE COPIED OR DISCLOSED WITHOUT WRITTEN CONSENT

Sheet 1	of 1
Drawing (C)	E and O E