

3M™ Portable Field Service Kit 8505

The Portable Field Service Kit 8505 is a small, lightweight kit that offers the same level of static control as the full-sized 3M™ Field Service Kit 8501, yet is small enough to fit in a shirt pocket.



| Specifications | Typical Value |
|-----------------------------|---|
| Resistance to Ground* (RTG) | < 10 ⁷ ohms |
| Resistance to Top* (RTT) | < 10 ⁷ -10 ⁸ ohms |
| Wrist Strap Ground Cord | 5 ft, 1 megohm resistor |
| Extension Ground Cord | 5 ft |
| Worksurface Ground Cord | 5 ft, 1 megohm resistor |
| Wrist Band | Fabric, Adjustable |
| Kit Includes | 1 – 14 x 19 inch dissipative mat with one pocket 1 – 3M™ Adjustable Fabric Wrist Band 2204 1 – 3M™ Alligator Clip 3038 Lightweight Coiled Ground Cords: 1 – 3M™ Wrist Strap Ground Cord 2240, 5 ft. 1 – 3M™ Extension Ground Cord 2243, 5 ft. 1 – 3M™ Worksurface Ground Cord 3063, 5 ft. Instructions |
| Part Numbers | |

8505 3M™ Portable Field Service Kit

*Tested via ANSI/ESD S4.1. Meets ANSI/ESD 20.20-2007.

RTG is the resistance from one point on the mat’s surface to the mat’s ground point, and is the fundamental electrical test for a mat. A proper RTG insures that a mat can conduct charge from a point on the surface to the mat ground point. The guideline in ESD STM-7.1 for RTG is 1x10⁶ to 1x10⁹ ohms. ANSI/ESD S-20.20 has an upper limit of <1x10⁹ ohms.

RTT is the resistance from one point on the mat’s surface to another point. A proper RTT insures the consistency of the mat’s resistance properties. The ESD STM-7.1 guideline for RTT is >1x10⁶ ohms.

Product Data Sheet

3M™ Portable Field Service Kit 8505

3M is a trademark of 3M Company.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for one year from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



Electronics Materials Solutions Division Static Control Products

926 JR Industrial Drive
Sanford, NC 27332-9733
Toll-Free: 866-722-3736
International: 919-718-0000
Email: 3mstaticinfo@mmm.com
www.3Mstatic.com

Please recycle. Printed in USA.
© 3M 2014. All rights reserved.
78-9102-1663-5 JHA