

## UCA0115: 3-to-1 xx90 Cable

## **Technical Datasheet**



## **Features**

- · Allows for 3x the capacity of any xx90 sized battery in 12 or 15V mode
- · Prevents inter-charging of batteries (see note 1)

## **Applications**

- · This adapter will operate any Auto 12V powered device from any xx90 battery:
  - UBI-390 / BB-390/U
  - BB-590/U
  - UBI-2590 (UBBL02) / BB-2590
  - UBBL09/B
  - UBI-2590 SMBus (UBBL10)
  - UBI-2590 HC SMBus (UBBL13)
  - UBI-2590 SF SMBus (UBBL36)
  - UB0023 (BA-5390A/U)
  - UB0031 (BA-5390 CFx)
  - UB0032 (BA-5390 SF CFx)

Technical Specifications			
Part No.	UCA0115		
Cable	(4) 18AWG conductors		
Max. Current	16A continuous per side		
Temperature Rating	-40°C to 70°C	-40°C to 70°C	
Length	1.17m (46in)		
Termination	Flying leads		
Weight	0.42lb		
Material	SVT, UL2464 jacketed		
Color	Black		
Pin Configuration	Black	Batt A -	
	Red	Batt A +	
	White	Batt B -	
	Brown	Batt B +	
Note 1	The state of the s	Whole batteries can be placed in cable at various states-of-charge in relation to each other. For	

states of charge.

best performance use with batteries at equal