

GS2AH180

External rotary handle, TeSys GS, red handle, front mounting, 2 positions I-O, NEMA 3R, for GS 800 to 1200A UL



Main

Range of Product	TeSys
Range	TeSys
Device short name	GS2AH
Product or Component Type	Rotary handle
Range compatibility	TeSys (TeSys GS) GS2T TeSys (TeSys GS) GS2V
Type of operating handle	External frontal
Handle colour	Red
Handle front plate colour	Yellow

Complementary

Handle positions	O-I
Rotary handle padlocking	With
Switch rated current	800 A 1200 A
Standards	CSA UL

Environment

NEMA degree of protection	NEMA 4/4X
---------------------------	-----------

Ordering and shipping details

Category	22640-IEC DISCONNECT-GS1,LK3
Discount Schedule	I11
GTIN	3606480512407
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.76 in (7.0 cm)
Package 1 Width	17.72 in (45.0 cm)
Package 1 Length	4.72 in (12.0 cm)
Package 1 Weight	19.40 oz (550.0 g)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------