



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	Installation guide
--------------------	--------------------

Physical

Color	Black
Depth	27.56 in (70 cm)
Height	6.26 in (15.9 cm)
Net Weight	55.56 lb(US) (25.2 kg)
Width	4.21 in (10.7 cm)

Conformance

Product certifications	CE
Standards	UL 1778

Environmental

Ambient air temperature for operation	64...81 °F (18...27 °C)
Operating altitude	0...3333 ft
Relative humidity	0...95 %
Ambient air temperature for storage	32...104 °F (0...40 °C)
Storage altitude	0...15000 ft (0.00...4572.00 m)
Storage Relative Humidity	0...95 %

Batteries & Runtime

Battery Placement	Internal Battery
Battery blocks per string	8
Battery Slots Empty	0
Included Battery Modules	0
Device mounting	Enclosed battery cartridge
Battery type	VRLA
Battery Volt-Amp-Hour Capacity	864 VAh



Ordering and shipping details

Package weight(Lbs)	59.52 lb(US) (27 kg)
---------------------	----------------------

Packing Units

Package 1 Height	7.09 in (18 cm)
Package 1 width	5.91 in (15 cm)
Package 1 Length	31.89 in (81 cm)
Number of Units in Package 3	32

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration