

Product data sheet

Specifications



metal conduit box UL, Altivar, Nema type1, IP21, for variable speed drive, size 6

VW3A9704

Main

Range of product	Altivar
Accessory / separate part category	Protection accessory
Accessory / separate part type	IP21 protection kit
Product compatibility	Variable speed drive ATV630 motor at 55 kW, normal duty 200...240 V Variable speed drive ATV630 motor at 75 kW, normal duty 200...240 V Variable speed drive ATV630 motor at 110 kW, normal duty 380...480 V Variable speed drive ATV630 motor at 132 kW, normal duty 380...480 V Variable speed drive ATV630 motor at 160 kW, normal duty 380...480 V Variable speed drive ATV630 motor at 90 kW, heavy duty 380...480 V Variable speed drive ATV630 motor at 110 kW, heavy duty 380...480 V Variable speed drive ATV630 motor at 132 kW, heavy duty 380...480 V Variable speed drive ATV610 motor at 110 kW 380...480 V Variable speed drive ATV610 motor at 132 kW 380...480 V Variable speed drive ATV610 motor at 160 kW 380...480 V Variable speed drive ATV930 motor at 55 kW, normal duty 200...240 V Variable speed drive ATV930 motor at 75 kW, normal duty 200...240 V Variable speed drive ATV930 motor at 110 kW, normal duty 380...480 V Variable speed drive ATV930 motor at 132 kW, normal duty 380...480 V Variable speed drive ATV930 motor at 160 kW, normal duty 380...480 V Variable speed drive ATV930 motor at 45 kW, heavy duty 200...240 V Variable speed drive ATV930 motor at 55 kW, heavy duty 200...240 V Variable speed drive ATV930 motor at 90 kW, heavy duty 380...480 V Variable speed drive ATV930 motor at 110 kW, heavy duty 380...480 V Variable speed drive ATV930 motor at 132 kW, heavy duty 380...480 V
Accessory / separate part destination	Variable speed drive
Range compatibility	Easy Altivar 610 Altivar Process ATV600 Altivar Process ATV900

Complementary

Kit composition	Instruction sheet Fixing accessories All the mechanical parts including a pre-cut plate for fixing the cable glands
Product weight	9 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	31.500 cm
Package 1 Width	37.100 cm
Package 1 Length	40.500 cm
Package 1 Weight	10.463 kg
Unit Type of Package 2	P12

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number of Units in Package 2	18
Package 2 Height	110.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	201.500 kg

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Efdd96fa-877d-491d-af5a-b4069bcf028e
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
PVC free	Yes

Use Again

 Repack and remanufacture	
Take-back	No