

Product data sheet

Characteristics

ACAC20002

CDU Flexible Fluid Piping - 300 Feet (91.4 Meters)



Overview

Lead time	Usually Ships within 4 Weeks
-----------	------------------------------

General

Provided Equipment	Installation guide
Maximum Recommended Flow Rate	18.5 gal(US)/min (1.17 l/s)
Piping Material	PEX-AL-PEX
Pressure Rating	150 psi (1034.21 kPa)
Fluid connection type	Unterminated
Minimum bending radius	8 in (203.20 mm)
Minimum Fluid Temperature	42 °F (6 °C)
Maximum Fluid Temperature	60 °F (16 °C)
Pressure Drop per foot (0.305m)	0.13 ft of water/ft 13.95 gal(US)/min (0.88 l/s)

Physical

Length	300 ft (91.44 m)
Color	White
Depth	42.01 in (106.7 cm)
Height	10.98 in (27.9 cm)
Product Weight	83.18 lb(US) (37.73 kg)
Width	42.01 in (106.7 cm)

Ordering and shipping details

GTIN	00731304241621
Package weight(Lbs)	87.19 lb(US) (39.55 kg)

Packing Units

Package 1 Height	12.52 in (31.8 cm)
Package 1 width	45.51 in (115.6 cm)
Package 1 Length	45.51 in (115.6 cm)
Number of Units in Package 3	6

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
-------------------	--

Contractual warranty

Warranty	1 year (parts only)
----------	---------------------