



Overview

Presentation	Ideal for retail, healthcare, and educational facilities, the wall rack offers an efficient solution for deploying server and networking equipment for edge computing applications. For areas with limited floor space. Designed to house your server, as well as network solutions such as network switches and patch panels. Rack hinges at the rear allowing for access to the back of the rack during installation and setup or while undergoing maintenance. The door is reversible allowing for the door to open direction desired to avoid interference with its surroundings. Optional 120V fan tray top-mounted and caster kit. Several APC Smart-UPS models low-profile provide easy UPS integration and mounting. 12U Wall mount cabinet, 16.8 to 20.8 inches mounting depth, 200lb weight capacity, 19" rack width, ships unassembled, 5 year APC warranty.
Lead time	Usually in Stock

Main

Number of rack unit	12U
---------------------	-----

Physical

Color	Black
Height	24.41 in (62 cm)
Width	23.58 in (59.9 cm)
Depth	23.58 in (59.9 cm)
Net Weight	40.30 lb(US) (18.28 kg)
Mounting Support	Wall
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	20.80 in (52.83 cm)
Minimum Mounting Depth	16.80 in (42.67 cm)
Rack Width	19"
Permanent permissible load	200 lb(US) (90.72 kg) static

Conformance

Standards	EIA-310E
-----------	----------

Ordering and shipping details

GTIN	731304317289
Package weight(Lbs)	50.99 lb(US) (23.13 kg)

Packing Units

Package 1 Height	11.54 in (29.3 cm)
Package 1 width	27.09 in (68.8 cm)
Package 1 Length	26.89 in (68.3 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------