



Overview

Presentation	Designed for high-density environments with standard features for speed of deployment and installation. Wide rack design provides space for passing cabling from front to back and ensures plenty of clearance at the back for rack accessories and limits interference with IT device hot-swap components. Very ideal for the blade, converged, and hyper-converged devices. A deeper rack design provides enough rack mounting space for even the deepest devices and still plenty of room for vertically mounting accessories. 48U height allows for an additional 6U of rack mounting space maximizing u-space per rack footprint.
Lead time	Usually in Stock

Main

Number of rack unit	48U
Provided equipment	Baying hardware Key(S) Leveling feet Mounting Hardware Pre-installed casters Side Panels

Physical

Color	Black
Height	88.90 in (225.8 cm)
Width	29.53 in (75 cm)
Depth	47.24 in (120 cm)
Net Weight	408.85 lb(US) (185.45 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	41.26 in (104.8 cm)
Minimum Mounting Depth	10.31 in (26.19 cm)
Rack Width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 16 gauge rear door 18 gauge roof 18 gauge side panels
Permanent permissible load	2250 Lb(US) (1020.58 kg) dynamic 3750 lb(US) (1700.97 kg) static

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

Ordering and shipping details

GTIN	731304259367
Package weight(Lbs)	444.94 lb(US) (201.82 kg)

Packing Units

Package 1 Height	94.49 in (240 cm)
Package 1 width	33.50 in (85.1 cm)
Package 1 Length	52.52 in (133.4 cm)
Number of Units in Package 3	1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------