

AR4000MVX431

APC NetShelter CX, Mini, Soundproof Server
Rack Enclosure, 100V to 240V, Dark Grey,
744H x 688W x 952D mm



Overview

Presentation	Netshelter CX Mini is specifically designed to house a complete small-office IT installation comprised of one or two servers, network hardware and peripheral devices. It combines extreme noise reduction and moderate thermal capacity with exceptional reliability and an all-inclusive, plug-and-play specification. Designed to accept tower form factor servers, the CX Mini can also be converted to accept rack form factor servers using a 12U rack mount conversion kit (AR4000MV12U). The resulting EIA rack is 600 mm/23.6" deep. NAM power cords sold separately, part number AR4605.
Lead time	Special Order - Call for Quoted Lead Times

Main

Main Input Voltage	115 V 120 V 200 V 208 V 220 V 230 V 240 V
Plug standard	NEMA 5-15P IEC 60320 C14
Cable length	4 ft (1.22 m)
Number of cables	1
Provided equipment	Brush strips Door Key(S) Lockable door Office-type Casters Power strip with (3) IEC receptacles Fans Removeable lockable rear panel Soundproofing Unpacking sheet

Physical

Color	Gray
Height	28.35 in (72 cm)
Width	27.17 in (69 cm)
Depth	36.61 in (93 cm)
Net Weight	165.35 lb(US) (75 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	27.56 in (70 cm)

Input

Input Frequency	50/60 Hz
-----------------	----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Conformance

Product Certifications	TAA compliance
------------------------	----------------

Ordering and shipping details

GTIN	731304298045
Package weight(Lbs)	176.37 lb(US) (80 kg)

Packing Units

Package 1 Height	29.53 in (75 cm)
Package 1 width	29.13 in (74 cm)
Package 1 Length	38.58 in (98 cm)
Number of Units in Package 3	1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Take-back	Take-back program available

Contractual warranty

Warranty	2 year (manufacturer's defect)
----------	--------------------------------