


Product availability: Stock - Normally stocked in distribution facility



Main

Product or component type	Communication card
Range compatibility	Altivar 312 Altivar 312 Solar
Communication port protocol	CANopen daisy chain
Electrical connection	1 connector RJ45, Modbus 1 removable screw terminal block for inputs/outputs 2 connectors RJ45, CANopen
Transmission rate	10, 20, 50, 125, 250, 500 kbps or 1 Mbps
Number of addresses	1...127

Complementary

Input/output number	AI2 and AI3: 2 analog input LI1...LI3: 3 logic input R2: 1 relay output
Physical interface	RS485 multidrop serial link
Transmission frame	RTU
Communication service	PDO 6 : can be configured, asynchronous, synchronous, cyclic asynchronous Communication monitoring node guarding and heartbeat CiA 402 profile PDO 1 : cannot be configured, asynchronous 1 receive SDO + 1 transmit SDO
Product weight	0.44 lb(US) (0.2 kg)

Ordering and shipping details

Category	22154 - ATV320/ATV312/ATV32 ACCESSORIES
Discount Schedule	CP4B
GTIN	00785901647881
Nbr. of units in pkg.	1
Package weight(Lbs)	0.34000000000000002
Returnability	Y
Country of origin	ID

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0931 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------