



### Overview

Presentation	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
Lead time	Usually Ships within 3 Weeks

### Main

Main Input Voltage	230 V
Main Output Voltage	240 V
Plug standard	IEC 60309
Provided Equipment	Installation guide

### Physical

Color	Gray
Height	5.00 in (12.7 cm)
Width	17.48 in (44.4 cm)
Depth	15.98 in (40.6 cm)
Net Weight	12.24 lb(US) (5.55 kg)

### Input

Input Frequency	60 Hz
Acceptable Input Voltage	200...240 V
Max line current	20 A

### Output

Maximum Total Current Draw per Phase	20 A
Number of power socket outlets	1 IEC 309

### Conformance

Product Certifications	UL Listed
------------------------	-----------





### Ordering and shipping details

GTIN	731304265337
Package weight(Lbs)	13.43 lb(US) (6.09 kg)

### Packing Units

Package 1 Height	5.00 in (12.7 cm)
Package 1 width	17.48 in (44.4 cm)
Package 1 Length	15.98 in (40.6 cm)

## Offer Sustainability

REACH Regulation	<a href="#"> REACH Declaration</a>
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	<a href="#"> Yes</a>
Environmental Disclosure	<a href="#"> Product Environmental Profile</a>
Circularity Profile	<a href="#"> End Of Life Information</a>
Take-back	Take-back program available

## Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------