



## Overview

Lead time	Usually Ships within 2 Weeks
-----------	------------------------------

## General

Provided equipment	Installation guide
--------------------	--------------------

## Physical

Depth	144.02 in (365.8 cm)
Height	5.00 in (12.7 cm)
Net Weight	40.48 lb(US) (18.36 kg)
Width	24.02 in (61 cm)

## Input

Plug standard	IEC 60309
Permissible voltage	200...240 V
Max line current	80 A
Nominal Input Voltage	208 V

## Output

Maximum Total Current Draw per Phase	80 A
Number of power socket outlets	1 IEC 60309 32 A
Cord Length	12 ft (3.66 m)
Output voltage	208 V

## Ordering and shipping details

GTIN	00731304252764
Package weight(Lbs)	43.98 lb(US) (19.95 kg)

## Packing Units

Package 1 Height	11.42 in (29 cm)
Package 1 width	25.20 in (64 cm)
Package 1 Length	25.20 in (64 cm)

## Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------