



Overview

Presentation	High availability, ruggedized power protection for shipboard and other transportation applications.
Lead time	Usually in Stock

Main

Main Input Voltage	208 V 220 V 230 V 240 V
Main Output Voltage	200 V 208 V 220 V 230 V 240 V
Other Output Voltage	208 V 220 V 230 V 240 V
Plug standard	IEC 60320 C20
Number of rack unit	1U
Cable length	8 ft (2.44 m)
Number of cables	1
Provided equipment	Installation guide Mounting Hardware User Manual

Environment

Ambient Air Temperature for Operation	32...131 °F (0...55 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...167 °F (-25...75 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Physical

Color	Black
Height	1.73 in (4.4 cm)
Width	17.01 in (43.2 cm)
Depth	10.98 in (27.9 cm)
Net Weight	11.22 lb(US) (5.09 kg)
Mounting Location	Front

Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input Frequency	47...63 Hz
Line Rated Current	16 A
Acceptable Input Voltage	100...240 V
Max line current	16 A
Input current limits	16 A
Load Capacity	3000 VA

Output

Maximum Total Current Draw per Phase	16 A
Number of power socket outlets	1 IEC 60320 C19
Number of power socket outlets	1
Protection Type	Without circuit breaker
Cord Length	8 ft (2.44 m)

Conformance

Product Certifications	DNV
------------------------	-----

Ordering and shipping details

GTIN	731304284697
Package weight(Lbs)	14.02 lb(US) (6.36 kg)

Packing Units

Package 1 Height	2.99 in (7.6 cm)
Package 1 width	15.00 in (38.1 cm)
Package 1 Length	22.01 in (55.9 cm)
Number of Units in Package 3	60

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------