

Cover plate, Linergy TR, 2 points, 2.2mm width, for screw terminals NSY TRV22,TRV42,TRV, grey, Set of 50

NSYTRAC22

Main

Range	Linergy	
Product name	Linergy TR	
Product or component type	Cover plate	
Device short name	TRA	
Accessory / separate part category	Insulation accessory	
Product compatibility	TRV screw terminal - passthrough terminal block, length = 47.7 mm TRV screw terminal - protective earth terminal block, length = 47.7 mm TRV screw terminal - blade disconnect terminal block, length = 55 mm	
Thickness	2.2 mm	

Complementary

Cable cross section	6 mm² 2.5 mm² 4 mm² 10 mm²	
number of connections	2	
Number of measurement input	2 1	
Quantity per set	Set of 50	
Product weight	2.4 g	
Colour	Grey	

Packing Units

_	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.400 cm
Package 1 Width	4.000 cm
Package 1 Length	4.700 cm
Package 1 Weight	2.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	50
Package 2 Height	3.000 cm
Package 2 Width	13.000 cm
Package 2 Length	17.000 cm

Package 2 Weight	131.000 g
Unit Type of Package 3	S04
Number of Units in Package 3	3600
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	9.950 kg

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration
Halogen-free status	Halogen free plastic parts product

Use Again

○ Repack and remanufacture		
Take-back	No	