

Product data sheet

Characteristics

8910DPA43V02Y181

Contactor, Definite Purpose, 40A, 3 pole, 25 HP at 575 VAC, 3 phase, 110/120 VAC 50/60 Hz coil, open, bulk packaged



Main

Product or Component Type	Definite Purpose Contactor
Line Rated Current	40 A
Number of Poles	3P
Pole contact composition	3 NO
Range of Product	DPA
Type of Packing	Bulk

Complementary

Maximum Horse Power Rating	3 Hp 115 V AC, 1 phase 7.5 Hp 230 V AC, 1 phase 10 Hp 230 V AC, 3 phase 20 Hp 460 V AC, 3 phase 25 hp 575 V AC, 3 phase
Locked rotor rated current	240 A 277 V AC 200 A 460 V AC 160 A 575 V AC
[Ue] rated operational voltage	600 V AC
[Uc] control circuit voltage	120 V AC 60 Hz 110 V AC 50 Hz
Phase	3 phase
Electrical Connection	Box lugs Quick connect terminals

Environment

Product Certifications	UL Recognized CSA
------------------------	----------------------

Ordering and shipping details

Category	21343-8910 DPA 3_(30 AMP)
Discount Schedule	CP1B
GTIN	785901229087
Returnability	No
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.00 in (7.62 cm)
Package 1 Width	2.40 in (6.096 cm)
Package 1 Length	3.70 in (9.398 cm)
Package 1 Weight	24.00 oz (680.389 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	20

Package 2 Height	7.00 in (17.78 cm)
Package 2 Width	6.00 in (15.24 cm)
Package 2 Length	21.00 in (53.34 cm)
Package 2 Weight	30.00 lb(US) (13.608 kg)

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------