

Product data sheet

Characteristics

9001SK1L35L

Illuminated push-button head, Harmony 9001SK, plastic, plastic guard flush, blue, 30mm, spring return, 24-28V



Main

Range of Product	Harmony 9001SK
Product or Component Type	Head for illuminated push-button
Device short name	9001SK
Bezel material	Plastic

Complementary

Mounting diameter	1.18 in (30 mm)
Shape of signaling unit head	Octagonal
Type of operator	Spring return
Operator profile	Blue flush, unmarked
Operator additional information	Plastic guard
Light source	incandescent
Bulb base	BA 9s
Light block supply	Direct 24...28 V AC/DC
Contacts type and composition	Without contact block
Standards	UL 508 JIS C 4520 EN/IEC 60947-1 EN/IEC 60947-5-4 JIS C 852 EN/IEC 60947-5-1 CSA C22.2 No 14
Product Certifications	UL 508 NEMA CSA LR25490 class 3211 03 UL listed file E78403 CCN NKCR
Protective treatment	TC
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Vibration resistance	7 gn 2...500 Hz IEC 60068-2-6
Shock resistance	50 gn IEC 60068-2-27
Electrical shock protection class	Class II IEC 61140
IP degree of protection	IP66 IEC 60529
NEMA degree of protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 NEMA 4X
Mechanical durability	5000000 cycles
Operating position	Any position
Net Weight	0.40 lb(US) (0.181 kg)

Ordering and shipping details

Category	21429-9001 SK,SKY
Discount Schedule	CS1
GTIN	785901158639
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.08 in (12.903 cm)
Package 1 Width	2.00 in (5.08 cm)
Package 1 Length	12.90 in (32.774 cm)
Package 1 Weight	6.40 oz (181.437 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------