



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	AC 3 phase
Provided Equipment	Installation guide Operations and maintenance manual

General

Compressor Type	Scroll
Refrigerant Charge	16.53 lb(US) (7.5 kg)

Physical

Color	Light gray
Height	37.91 in (963 mm)
Width	39.37 in (1000 mm)
Depth	17.72 in (450 mm)
Net Weight	385.81 lb(US) (175 kg)

Input

Input Frequency	50-60 Hz
-----------------	----------

Conformance

Product Certifications	UL RCM
------------------------	-----------

Ordering and shipping details

GTIN	731304426998
------	--------------

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	1 year (parts only), 1 year on-site repair or replace with factory authorized Start-Up
----------	--