



## Overview

Lead time	Usually in Stock
-----------	------------------

## Physical

Connector B	SUB-D 9 female Smart Signaling
Height	2.24 in (5.7 cm)
Cable length	6.56 ft (2.00 m)
Connector A	RJ45 male
Depth	4.25 in (10.8 cm)
Net Weight	0.31 lb(US) (0.14 kg)
Width	8.74 in (22.2 cm)

## Output

Number of port	1
----------------	---

## Ordering and shipping details

GTIN	00731304310815
Package weight(Lbs)	0.31 lb(US) (0.14 kg)

## Packing Units

Package 1 Height	2.24 in (5.7 cm)
Package 1 width	8.74 in (22.2 cm)
Package 1 Length	4.25 in (10.8 cm)
SCC14	10731304310812

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Lead free	Yes

WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	Take-back program available