



Overview

Lead time	Usually in Stock
-----------	------------------



General

Provided Equipment	User Manual Rack Mounting brackets
--------------------	---------------------------------------

Physical

Color	Black
Depth	24.02 in (61 cm)
Height	3.50 in (8.9 cm)
Product Weight	95.20 lb(US) (43.18 kg)
Width	17.52 in (44.5 cm)

Input

Input current limits	26 A
Load Capacity	5000 VA
Input Frequency	60 Hz +/- 3 Hz
Number of input connectors	1 Hard Wire 3-wire (2PH + G)
Nominal Input Voltage	208 V

Output

Efficiency	90 %
Output connector type	Hard Wire 3-wire (H N + E) 1

Conformance

Product Certifications	CSA UL Listed
Standards	UL 1778

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	00731304249153
Package weight(Lbs)	110.23 lb(US) (50 kg)

Packing Units

Package 1 Height	10.00 in (25.4 cm)
Package 1 width	24.49 in (62.2 cm)
Package 1 Length	37.52 in (95.3 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------